

SAFE-T_{station}

Upon easy installation, the SAFE-T Station immediately starts preventing burn injuries by enclosing the sample collection container before discharging hot liquid A.C.

Large enough to enclose a one-gallon sample, the operator can view the fill level of the collection container through our SAFE-T Station's viewing glass door. The SAFE-T Station takes safety one step further by not allowing operation of the plug valve handle unless the enclosure door is securely shut tight in the closed position.

Versatility is the name of the game, allowing the SAFE-T Station to be fitted with either 3" or 4" thermal jacketed liquid asphalt lines. Hotmix Parts® made sure that our SAFE-T Station will not disrupt your inline A.C. process by adding a double flanged A.C. pass through.

A lockable safety latch holds the plug valve handle in the closed position when not in use, ensuring that all new samples are fresh from the line.



 Stansteel® |  HOTMIX
parts & service

We Make Your Plant Run Better.

800-826-0223 | stansteel.com | hotmixparts.com